

Speeds & Feeds

Product Table: End Mills for Steels & High Temp Alloys - Ball - 2 & 3 Flute - Stub Flute Characteristics: 1.5x Length of Cut, 2 & 3 Flutes Series: BEF-XXX-XXX, BEF-XXX-XXX-X, BEFM-XXX-XXX

Material	Hardness (HBn)	SFM	Chip Load (IPT) By Cutter Diameter													Depth of Cut	
				0.015	0.031	0.047	0.062	0.078	0.093	0.125	0.187	0.250	0.312	0.375	0.500	Radial	Axial
Tool Steels: D, H, M, T, S series	350 - 400	100	Slotting	.00006	.00012	.00018	.00023	.00029	.00035	.00047	.00070	.00094	.00123	.00147	.00196	1x Dia	.4x Dia
	400 - 425	80															
Stainless Steels : 40x, 41x, 42x, 43x, 44x, 13-8, 15-5, 15-7, 17-4, 17-7	275 - 300	160															
	300 - 350	140	Roughing	.00007	.00015	.00022	.00030	.00037	.00044	.00060	.00089	.00119	.00156	.00188	.00250	.4x Dia	.5x7x Dia
Titanium: All alloys	275 - 300	200															
	300 - 350	125															
	350 - 400	75	Finishing	.00009	.00019	.00029	.00039	.00049	.00058	.00078	.00117	.00156	.00204	.00246	.00327	.1x Dia	.5x - 1x Dia
	400 - 425	75															
Nickel Alloys: Inconel, Hastelloy, Waspalloy, Monel, Nimonic, Haynes, Discoloy, Incoloy	275 - 300	80															
	300 - 350	60	Max	.00011	.00023	.00035	.00046	.00058	.00070	.00094	.00140	.00187	.00245	.00295	.00393	-	-
	350 - 400	50															
	400 - 425	40															

Please note:

All posted speed and feed parameters are suggested starting values that may be increased given optimal setup conditions. If less than minimum Axial or Radial DOC values are used, increased feed rates are possible. If greater than maximum Axial or Radial DOC values are used, decreased feed rates may be needed. If you require additional information, Harvey Tool has a team of technical experts available to assist you through even the most challenging applications. Please contact us at **800-421-8065** or **micro100tech@harveyperformance.com**.

WARNING: Cutting tools may shatter under improper use. Government regulations require use of safety glasses and other appropriate safety equipment in the vicinity of use.